

VIBRATION DAMPING SHEETS

Key Features

- Usable for wide range of loads: Divide for light load, add for heavy load
- Just place it under the device. Removable anytime
- Stable with small resonance magnification and little horizontal distortion



Specifications

Part number	Optimum load (Kg/1 sheet)	Resonance point (Hz)	Resonance Magnification (dB)	Recommended Frequency (Hz)	Deflection (mm)	Color
VI00045	0.5 ~ 2	27 ~ 21	6	38 ~	1.4 ~ 3.0	Yellow
VI00046	2 ~ 5	29 ~ 23	8	40 ~	1.5 ~ 2.5	Green
VI00047	5 ~ 15	26 ~ 18	13	37 ~	1.1 ~ 2.2	Orange
VI00048	15 ~ 50	22 ~ 15	20 ~ 18	30 ~	0.7 ~ 2.0	Blue

Note :

Place the sheets (or portions of them) so that the vibrating object becomes stable.
Place the sheet so that the load of the vibrating object is spread evenly on the projections.
Placing a flat plate on the top surface of the sheet helps.
Remove the protective PET film from the bottom surface before use.

